



# YA4CL2TC14, 4 AWG Cu , 2-Hole, 1/4" Stud, 5/8" Spacing, Std

By Burndy  
Catalog # [YA4CL2TC14](#)

4 AWG, CU, 2 Hole, 1/4" Stud, 5/8" Spacing, Standard Barrel, Inspection Window, Tin Plated



## Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

## Application

Wire Termination

## Specifications

|                                    |                                                      |
|------------------------------------|------------------------------------------------------|
| Certification - UL Recognized      | No                                                   |
| Buy American Compliant             | Contact Manufacturer                                 |
| Certification - cULus              | No                                                   |
| EU RoHS Indicator                  | Yes                                                  |
| Buy America(n) Qualified           | BABA Compliant (All status valid till December 2026) |
| Industry Standard(s)               | UL 486A-486B                                         |
| Certification - ETL                | No                                                   |
| Standards - Industry Standards Met | UL 486A-486B                                         |
| Standards - RoHS Compliance Status | CM                                                   |
| UL Listed                          | Yes                                                  |
| Certification - CSA Approved       | Yes                                                  |

## Conductor

|                                        |                           |
|----------------------------------------|---------------------------|
| Conductor - Material                   | COPPER                    |
| Conductor - Copper Str Size            | 4 AWG                     |
| Conductor - Copper DLO Size Range      | N/A                       |
| Conductor Size                         | 4 AWG                     |
| Conductor - Copper Str Navy Size Range | 40 (19) Navy-50 (19) Navy |
| Conductor - Copper Str Navy Size       | 40 (19) Navy              |
| Conductor - Copper Solid Size          | #4 AWG                    |
| Conductor Type                         | CODE                      |
| Conductor - Copper Str Size Range      | 4 AWG                     |

## Configuration

|                                      |                 |
|--------------------------------------|-----------------|
| Physical Attribute - Number of Holes | 2               |
| Number of Pad Holes                  | 2               |
| Connector Type                       | STANDARD BARREL |

## Current

|                   |       |
|-------------------|-------|
| Voltage Rating    | 35 kV |
| Voltage - Maximum | 35000 |

## Dimensions

|                                   |           |
|-----------------------------------|-----------|
| Dimension - Pad Width inch        | 0.5 in    |
| Package Height                    | 0.000 in  |
| Dimension - Hole Size fraction    | 1/4       |
| Package Weight                    | 0.000 lb. |
| Package Length                    | 0.000 in  |
| Package Width                     | 0.000 in  |
| Dimension - Outside Diameter inch | 0.34 in   |
| Dimension - Hole Size mm          | 6.9 mm    |
| Dimension - Hole Size inch        | 0.27      |
| Dimension - Strip Length inch     | 7/8 in    |
| Dimension - Stud Size inch        | 1/4       |
| Dimension - Stud Size fraction    | 1/4       |
| Dimension - Bolt Hole Size inch   | 0.21 in   |
| Dimension - Bolt Size fraction    | 1/4       |
| Physical Attribute - Tongue Angle | Straight  |
| Dimension - B Length fraction     | 13/16 in  |
| Dimension - Z inch                | 0.27      |
| Dimension - B Length inch         | 0.81 in   |
| Dimension - N inch                | 0.25 in   |
| Dimension - Bolt Size inch        | 0.25      |
| Dimension - Length Overall inch   | 2.24 in   |

## General

|                        |                                                                              |
|------------------------|------------------------------------------------------------------------------|
| Trade Name             | HYLUG™                                                                       |
| Die Index              | 8                                                                            |
| Feature - Barrel Type  | Standard                                                                     |
| Feature - Barrel Style | <ul style="list-style-type: none"><li>• Chamfered</li><li>• Skived</li></ul> |
| Plated                 | Y                                                                            |
| Color Code             | Gray                                                                         |

|                             |                             |
|-----------------------------|-----------------------------|
| Physical Attribute - Tongue | Standard                    |
| Type                        |                             |
| Sub Brand                   | HYLUG                       |
| UPC                         | 781810503560                |
| Type                        | Standard Barrel, Tin Plated |
| Material                    | Copper                      |
| Plating Type                | Tin Plating                 |
| Finish Type                 | Tin-Plated                  |
| UPC 12 Digit                | 781810503560                |
| UPC 14 Digit GTIN           | 00781810503560              |

Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 1  |
| Carton Quantity       | 50 |

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand