



YA4CL2TC14E290, 4 AWG Cu, 2-Hole, 1/4" on 3/4", Std, 90 Deg

By Burndy

Catalog # [YA4CL2TC14E290](#)

4 AWG, CU, 2 Hole, 1/4 Stud, 3/4 IN Spacing, Standard Barrel, Inspection Window, 90 Degree

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	4 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	4 AWG
Conductor - Copper Str Navy Size Range	40 (19) Navy-50 (19) Navy
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	4 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2



Connector Type STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.50 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Dimension - Height inch	1.22 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	42 mm
Dimension - Outside Diameter inch	0.34 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	7/8
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	90 Degree
Angle - Pad	90 °
Dimension - B Length fraction	13/16 in
Dimension - Z inch	0.33 in
Dimension - B Length inch	0.81 in
Dimension - D inch	1.39 in
Dimension - N inch	0.31 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	1.66 in

General

Trade Name	HYLUG™
Die Index	8
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Gray

Physical Attribute - Tongue	Standard	UPC 14 Digit GTIN	00781810195130
Type		Logistics	
UPC	781810195130		
Type	Standard Barrel, Tin Plated	Minimum Pack Quantity	10
Material	Copper	Carton Quantity	100
Plating Type	Tin Plating		
Finish Type	Tin-Plated	Product Assets	
UPC 12 Digit	781810195130	Catalog [English]	



A Hubbell brand