



YA4CL2TC38, 4 AWG Cu, 2-Hole, 3/8" Stud, 1" Spacing, Std

By Burndy

Catalog # [YA4CL2TC38](#)

4 AWG, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Standard Barrel, Inspection Window



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	4 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	4 AWG
Conductor - Copper Str Navy Size Range	40 (19) Navy-50 (19) Navy
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	4 AWG

Configuration

Physical Attribute - Number of Holes	2
--------------------------------------	---

Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.58 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	75 mm
Dimension - Outside Diameter inch	0.34 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	7/8 in
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	13/16 in
Dimension - Z inch	0.42
Dimension - B Length inch	0.81 in
Dimension - D inch	1.83 in
Dimension - N inch	0.34 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	2.96 in

General

Trade Name	HYLUG™
Die Index	8
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Gray
Physical Attribute - Tongue Type	Standard

Sub Brand	HYLUG	Logistics	
UPC	781810018187	Carton Quantity	50
Type	Standard Barrel, Tin Plated	Product Assets	
Material	Copper	Catalog [English]	
Plating Type	Tin Plating	Installation Manual [English]	
Finish Type	Tin-Plated	Installation Manual [French, English]	
UPC 12 Digit	781810018187		
UPC 14 Digit GTIN	00781810018187		

