



YA4CL5, #4 AWG Cu, 1-Hole, 7/16" Stud, Standard Barrel

By Burndy
Catalog # [YA4CL5](#)

4 AWG, 40 Navy, Cu, 1-Hole, 7/16" Stud, Standard Barrel, Gray / 8 or 346 Index



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	4 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	4 AWG
Conductor - Copper Str Navy Size Range	40 (19) Navy-50 (19) Navy
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor - Copper Solid Size Range	4 AWG
Conductor - Copper Solid Size Range	4 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	4 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.64 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	52 mm
Dimension - Outside Diameter inch	0.34 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Stud Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	13/16 in
Dimension - Z inch	0.48 in
Dimension - B Length inch	0.81 in
Dimension - D inch	0.98 in
Dimension - N inch	0.47 in
Dimension - Inside Diameter inch	0.25 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	2.03 in

General

Trade Name	HYLUG™
Die Index	8
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Gray
UPC	781810192269

Type	Standard Barrel, Tin Plated	Pallet Quantity	76800
Material	Copper	Carton Quantity	100
Plating Type	Tin - Electro Plated		
Finish Type	Tin-Plated		
UPC 12 Digit	781810192269		
UPC 14 Digit GTIN	00781810192269		

Logistics

Minimum Pack Quantity100



Operational

Temperature Rating194

Product Assets

Catalog [\[English\]](#)