



YA4CLNKBOX, 4 AWG Cu, 1/4" Stud, Standard, Nickel Plated

By Burndy

Catalog # [YA4CLNKBOX](#)



4 AWG Cu, 1-Hole, 1/4" Stud, Standard Barrel, Inspection Window, Nickel Plated

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	N/A
Conductor Size	4 AWG
Conductor - Copper Str Navy Size Range	40 (19) Navy-50 (19) Navy
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	4 AWG
Conductor - Copper Str Size	4 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.50 in
Dimension - Bolt Hole Size inch	0.27 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	13/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.33 in
Dimension - L Length Overall mm	44 mm
Dimension - B Length inch	0.81 in
Dimension - Outside Diameter inch	0.34 in
Dimension - D inch	0.64 in
Dimension - N inch	0.31 in
Dimension - Hole Size mm	6.9 mm
Dimension - Bolt Size inch	0.25
Dimension - Hole Size inch	0.27
Dimension - Length Overall inch	1.74 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size fraction	1/4

General

Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Gray
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard
Die Index	8
UPC	781810069646
Type	Standard Barrel, nickel Plated
Material	Copper
Plating Type	Nickel Plating
Finish Type	Nickel Plated

UPC 12 Digit	781810069646	Carton Quantity	50
UPC 14 Digit GTIN	00781810069646		
		Product Assets	
		Catalog [English]	

Logistics

Minimum Pack Quantity 50



A Hubbell brand