



YA6C2L52, 6 AWG Cu, 2-Hole, 1/4" Stud, 1/2" Spacing, Std

By Burndy
Catalog # [YA6C2L52](#)

6 AWG, CU, 2-Hole, 1/4" Stud, 1/2" Spacing, Standard Barrel, Inspection Window, Blue / 7 or 374 Index



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Yes
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2026) • Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	6 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	6 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	6 AWG

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.45 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	48 mm
Dimension - Outside Diameter inch	0.29 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	9/16 in
Dimension - Z inch	0.33 in
Dimension - B Length inch	0.54 in
Dimension - D inch	0.58 in
Dimension - N inch	0.25 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	1.88 in

General

Trade Name	HYLUG™
Die Index	7
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived

Plated	Y
Color Code	Blue
Sub Brand	TERMINALS, HYLUG
UPC	781810018859
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810018859

Logistics

Minimum Pack Quantity	1
Carton Quantity	50

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)

