



YA6C2TC14, 6 AWG Cu, 2-Hole, 1/4" Stud, 5/8" Spacing, Long

By Burndy

Catalog # [YA6C2TC14](#)

6 AWG, Copper, 2-Hole, 1/4" Stud, 5/8" Spacing, Long Barrel, Tin Plated, Blue / 7 or 374 Index

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	6 AWG
Conductor Size	6 AWG
Conductor - Copper Str Navy Size Range	30 (19) Navy
Conductor - Copper Str Navy Size	30 (19) Navy
Conductor - Copper Solid Size	6 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	6 AWG

Configuration



Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.45
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	67
Dimension - Outside Diameter inch	0.29
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size inch	1/4 in
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.34 in
Dimension - B Length inch	1.12
Dimension - N inch	0.31
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	2.65

General

Trade Name	HYLUG™
Die Index	7
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Blue
Physical Attribute - Tongue Type	Straight
Sub Brand	HYLUG

UPC	781810019511
Type	Long Barrel, Tin Plated
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810019511
UPC 14 Digit GTIN	00781810019511

Logistics

Minimum Pack Quantity1

Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [French, English]



A Hubbell brand