



YA6CL190, #6 AWG Cu, 1-Hole, Standard Barrel, 90 Degree

By Burndy
Catalog # [YA6CL190](#)

Copper Compression Terminal



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	6 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	6 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	6 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.42 in
Package Height	0.000 in
Dimension - Hole Size fraction	#10
Dimension - Height inch	0.94 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	18 mm
Dimension - Outside Diameter inch	0.29 in
Dimension - Hole Size mm	5.3 mm
Dimension - Hole Size inch	0.21
Dimension - Strip Length inch	9/16
Dimension - Stud Size inch	• #10 • #8
Dimension - Stud Size fraction	#10
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	#8-#10
Physical Attribute - Tongue Angle	90 Degree
Angle - Pad	90 °
Dimension - B Length fraction	9/16 in
Dimension - Z inch	0.27 in
Dimension - B Length inch	0.54 in
Dimension - D inch	0.49 in
Dimension - N inch	0.22 in
Dimension - Bolt Size inch	0.21
Dimension - Length Overall inch	0.72 in

General

Trade Name	HYLUG™
Die Index	7
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Blue
Physical Attribute - Tongue Type	Standard
UPC	781810085479
Type	Standard Barrel, Tin Plated

Material	Copper	Minimum Pack Quantity	1
Plating Type	Tin - Electro Plated	Carton Quantity	100
Finish Type	Tin-Plated		
UPC 14 Digit GTIN	00781810085479		

Product Assets

[Catalog \[English\]](#)

Logistics



A Hubbell brand