



YA8C2LN, 8 AWG Cu, 2-Hole NEMA, Standard Barrel

By Burndy

Catalog # [YA8C2LN](#)

8 AWG, CU, 2 Hole, 1/2 Stud, 1-3/4 IN Spacing, Standard Barrel, Inspection Window



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	8 AWG
Conductor - Copper Flex K Size	"8 AWG"
Conductor - Copper Flex M Size	"8 AWG"
Conductor - Copper Str Size	"8 AWG"
Conductor - Copper Flex G Size	"8 AWG"
Conductor - Copper Str	"8 AWG"
Compact Size	
Conductor - Copper DLO Size	8 AWG
Conductor Size	8 AWG
Conductor - Copper Flex H Size	"8 AWG"
Conductor - Copper Str Navy	23 (7) Navy
Size Range	
Conductor - Copper Str Navy	23
Size	
Conductor - Copper Solid Size	6 Sol-8 Sol
Conductor Type	CODE/FLEX

Conductor - Copper Str Size	8 AWG
Range	
Conductor - Copper Flex I Size	"8 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.83 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	95 mm
Dimension - Outside Diameter inch	0.27 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	7/16 in
Dimension - Z inch	0.64 in
Dimension - B Length inch	0.44 in
Dimension - D inch	1.26 in
Dimension - N inch	0.62 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	3.75 in

General

Trade Name	HYLUG™
------------	--------

Die Index	49	Finish Type	Tin-Plated
Feature - Barrel Type	Standard	UPC 14 Digit GTIN	00781810044612
Feature - Barrel Style	Chamfered		
Plated	Y	Logistics	
Color Code	Red	Carton Quantity	50
Sub Brand	TERMINALS, HYLUG		
UPC	781810044612	Product Assets	
Type	Standard Barrel, Tin Plated	Catalog [English]	
Material	Copper	Installation Manual [English]	
Plating Type	Tin - Electro Plated	Installation Manual [French, English]	



A Hubbell brand