



YA8CL245, Compression Terminal, #8 AWG, 23 Navy, 1-Hole, 5/16" Stud, Standard Barrel, 45 Degree

By Burndy
Catalog # [YA8CL245](#)



Copper HYLUG™, Single Hole W/ Insp Window, #8 AWG, 23 Navy, 600 V-35 kV, 5/16" Stud, Red, 49 Index, Electro-Tin plated, 45 Degree Bend.

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YA8CL245
Color Code	Red
Connector Type	STANDARD BARREL
Die Index	49
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810019214
UPC 14 Digit GTIN	00781810019214

Dimensions

Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125

Dimension - D inch	0.70 in
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	34 mm
Dimension - Length Overall inch	1.34 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.52 in
Dimension - Strip Length inch	7/16
Dimension - Stud Size fraction	5/16
Dimension - Stud Size inch	5/16
Dimension - Z (inch)	0.36 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	8 AWG
Conductor - Copper DLO Size Range	N/A
Conductor - Copper Flex G Size	"8 AWG"
Conductor - Copper Flex H Size	"8 AWG"
Conductor - Copper Flex I Size	"8 AWG"
Conductor - Copper Flex K Size	"8 AWG"
Conductor - Copper Flex M Size	"8 AWG"
Conductor - Copper Solid Size	6 Sol-8 Sol
Conductor - Copper Solid Size Range	8-6 Sol
Conductor - Copper Str Compact Size	"8 AWG"
Conductor - Copper Str Navy Size	23

Conductor - Copper Str Navy Size Range	23 (7) Navy
Conductor - Copper Str Size	"8 AWG"
Conductor - Copper Str Size Range	8 AWG
Conductor - Material	COPPER
Conductor Size	8 AWG
Conductor Type	CODE/FLEX
Wire Size	8 AWG

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	50

Product Assets

- Catalogs - [BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- Customer Notices - [Prop 65 Notice](#)
- Interactive Catalog - [BURNDY Full-Line Digital Catalog](#)
- Sales Drawings - [se209240_2](#)
- Specifications - [YA8CL245](#)
- Video - [HYDENT Compression Terminal Overview Video](#)



A Hubbell brand