



YA8CLNT8, 8 AWG CU, #8 Stud, Standard, Narrow Tongue

By Burndy

Catalog # [YA8CLNT8](#)

8 AWG, CU, 1 Hole, #8 Stud, Standard Barrel, Inspection Window, Narrow Tongue



Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	8 AWG
Conductor - Copper Flex K Size	"8 AWG"
Conductor - Copper Flex M Size	"8 AWG"
Conductor - Copper Str Size	"8 AWG"
Conductor - Copper Flex G Size	"8 AWG"
Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Compact Size	"8 AWG"
Conductor - Copper DLO Size	8 AWG
Conductor Size	8 AWG
Conductor - Copper Flex H Size	"8 AWG"
Conductor - Copper Str Navy Size	23
Conductor - Copper Solid Size	6 Sol-8 Sol
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	8 AWG

Conductor - Copper Flex I Size "8 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.33 in
Package Height	0.000 in
Dimension - Hole Size fraction	#8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	30 mm
Dimension - Outside Diameter inch	0.27 in
Dimension - Hole Size mm	4.6 mm
Dimension - Hole Size inch	0.18
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	#8
Dimension - Stud Size fraction	#8
Dimension - Bolt Size fraction	#8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	7/16 in
Dimension - Z inch	0.25 in
Dimension - B Length inch	0.44 in
Dimension - D inch	0.47 in
Dimension - N inch	0.22 in
Dimension - Inside Diameter inch	0.18 in
Dimension - Bolt Size inch	0.18
Dimension - Length Overall inch	1.18 in

General

Trade Name	HYLUG™
Die Index	49

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Red
Sub Brand	TERMINALS, HYLUG
UPC	781810229002
Type	YA-L-NT
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated

UPC 14 Digit GTIN00781810229002

Logistics

Carton Quantity100

Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [French, English]



A Hubbell brand