



YAB28CG53, Compression Terminal, 4/0 Fles, M8 Stud, Brazed Lug

By Burndy
Catalog # [YAB28CG53](#)



Copper Compression Terminal

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	4/0 AWG
Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Solid Size Range	4/0 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.19 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.62 in
Dimension - L Length Overall mm	82 mm
Dimension - B Length inch	1.28 in
Dimension - Outside Diameter inch	0.77 in
Dimension - D inch	1.25 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	10 mm
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size inch	0.38
Dimension - Length Overall inch	3.22 in
Dimension - Strip Length inch	1-1/2
Dimension - Stud Size fraction	5/16

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Purple
Trade Name	HYLUG™
Die Index	15
UPC	781810468333
Type	Standard Barrel, Tin Plated
Material	COPPER
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810468333
UPC 14 Digit GTIN	00781810468333

Logistics

Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand