

YAD1038, Uninsulated Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [YAD1038](#)

Uninsulated Ring Terminal For 12 - 10 AWG



Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hold for an easy visual check of wire insertion
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For control wiring and other standard duty applications

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes

UL Listed	Yes
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
----------------	-------------

Configuration

Connector Type	Ring Terminal
----------------	---------------

Dimensions

Dimension - Bolt Size fraction	3/8
--------------------------------	-----

General

Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
Material	Copper
UPC	781810806418

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)