



YAD146F, Uninsulated Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAD146F](#)

Uninsulated Fork Terminal For 16 - 14 AWG



Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hole for an easy visual check of wire insertion
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For Use in compression connections

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	• 20 AWG • 18 AWG • 16 AWG • 14 AWG
Conductor - Copper Solid Size	• 20 AWG • 18 AWG • 17 AWG • 16 AWG • 15 AWG • 14 AWG

Conductor - Copper Solid Size Range	20 AWG -14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor Type	CU C Solid-Size, CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	17 mm
Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	• #4 • #5 • #6
Dimension - Z inch	0.25 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Length Overall inch	0.68 in

General

Trade Name	HYLUG™
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Type	Fork Tongue
UPC 12 Digit	781810806456
UPC 14 Digit GTIN	00781810806456
Material	Copper
Plating Type	Tin
UPC	781810806456

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000

Pallet Quantity 99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand