



YAD186F, Uninsulated Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAD186F](#)

Uninsulated Fork Terminal For 22 - 18 AWG



Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hole for an easy visual check of wire insertion
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For Use in compression connections

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	• 22 AWG • 20 AWG • 18 AWG
Conductor - Copper Solid Size	• 22 AWG • 20 AWG • 18 AWG
Conductor - Copper Solid Size Range	22 AWG-18 AWG
Conductor - Copper DLO Size Range	N/A
Conductor Size	22 - 18 AWG

Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Type	CU C Solid-Size, CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	17 mm
Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	• #4 • #5 • #6
Dimension - Z inch	0.25 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Length Overall inch	0.68 in

General

Trade Name	HYLUG™
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Fork
Plated	Y
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Type	Fork Tongue
UPC 12 Digit	781810806180
UPC 14 Digit GTIN	00781810806180
Material	Copper
Plating Type	Tin
UPC	781810806180

Logistics

Minimum Pack Quantity	2000
-----------------------	------

Carton Quantity2000

Pallet Quantity99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand