



# YAE10N110BFBOX, Nylon Block Fork Terminal For 12 - 10 AWG

By Burndy  
Catalog # [YAE10N110BFBOX](#)

Nylon Block Fork Terminal For 12 - 10 AWG



## Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

## Application

Power Connector

## Specifications

|                               |                      |
|-------------------------------|----------------------|
| Certification - cULus         | No                   |
| EU RoHS Indicator             | Yes                  |
| Certification - UL Recognized | No                   |
| Certification - ETL           | No                   |
| Standards - RoHS Compliance   | CM                   |
| Status                        |                      |
| Certification - CSA Approved  | No                   |
| UL Listed                     | No                   |
| Buy America(n) Qualified      | Contact Manufacturer |

## Conductor

|                                   |                 |
|-----------------------------------|-----------------|
| Conductor Size                    | 12 - 10 AWG     |
| Conductor - Copper Str Size Range | 12 AWG - 10 AWG |
| Conductor Type                    | CU C Str-Size   |

## Configuration

|                |                     |
|----------------|---------------------|
| Connector Type | Block Fork Terminal |
|----------------|---------------------|

## Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

## Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Z inch              | 0.29 in |
| Dimension - L Length Overall mm | 26 mm   |
| Dimension - Pad Width inch      | 0.30 in |
| Dimension - Bolt Size fraction  | #4 - #6 |
| Dimension - Strip Length inch   | 3/8     |
| Dimension - Stud Size inch      | #4 - #6 |
| Dimension - Length Overall inch | 1.02 in |

## General

|                                  |                |
|----------------------------------|----------------|
| Sub Brand                        | INSULUG        |
| Insulation Type                  | Nylon          |
| Physical Attribute - Tongue Type | Fork           |
| Trade Name                       | INSULUG™       |
| Plated                           | Y              |
| Insulation                       | Y              |
| Type                             | YAE-N          |
| UPC 12 Digit                     | 781810524404   |
| UPC 14 Digit GTIN                | 00781810524404 |
| Material                         | Copper         |
| Plating Type                     | Unplated       |
| UPC                              | 781810524404   |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 50    |
| Carton Quantity       | 100   |
| Pallet Quantity       | 99999 |

## Product Assets

[Catalog \[English\]](#)