

YAE10N11BFBOX, Nylon Block Fork Terminal For 12 - 10 AWG

By Burndy
Catalog # [YAE10N11BFBOX](#)

Nylon Block Fork Terminal For 12 - 10 AWG



Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

Power Connector

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	4.000 in
----------------	----------

Package Width	3.000 in
Package Weight	0.290 lb.
Dimension - Z inch	0.29 in
Dimension - L Length Overall mm	26 mm
Dimension - Pad Width inch	0.33 in
Package Height	1.500 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Strip Length inch	3/8
Dimension - Stud Size inch	#6 - #8
Dimension - Length Overall inch	1.02 in

General

Sub Brand	INSULUG
Insulation Type	Nylon
Physical Attribute - Tongue Type	Fork
Trade Name	INSULUG™
Plated	Y
Insulation	Y
Type	YAE-N
UPC 12 Digit	781810524428
UPC 14 Digit GTIN	00781810524428
Material	Copper
Plating Type	Unplated
UPC	781810524428

Logistics

Minimum Pack Quantity	50
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)