



YAE14N1BOX, Nylon Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAE14N1BOX](#)



Nylon Ring Terminal For 16 - 14 AWG

Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

Application

For Use On: 600 Volts Maximum, 105 Deg C Maximum

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Aircraft Size	• AN 16 • AN 14
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type	Ring Terminal
----------------	---------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	23 mm
Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	3/16
Dimension - Stud Size inch	• #6 • #8
Dimension - Z inch	0.28 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Length Overall inch	0.92 in
Dimension - N inch	0.16 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Military Specification	MS25036
Sub Brand	INSULUG
Color Code	Blue
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Style	Shrouded
Type	YAE-N
UPC 12 Digit	781810563106
UPC 14 Digit GTIN	00781810563106
Material	Copper
Plating Type	Tin
UPC	781810563106

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200

Pallet Quantity99999

Product Assets

Operational

[Catalog \[English\]](#)

Temperature Rating105°C



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YAE14NIBOX-SPEC-EN | REV 4/2026