



YAE14N43, Nylon Ring, 16-14 AWG, #4-6 Stud

By Burndy
Catalog # [YAE14N43](#)

Nylon Ring Terminal For 16 - 14 AWG, #4-6 Stud, Multi-Finger Insulation Grip, Deep V Groove, Bulk Package



Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

Application

For use on copper compression connections

Specifications

Certification - UL Recognized	No
Buy American Compliant	Yes
Certification - cULus	No
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2026) • Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	16 AWG - 14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	21 mm
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#4 - #6
Dimension - Bolt Size fraction	#4 - #6
Dimension - B Length fraction	1/4 in
Dimension - Z inch	0.213 in
Dimension - B Length inch	0.25 in
Dimension - N inch	0.13 in
Dimension - Length Overall inch	0.819 in
Cable Insulation Diameter Maximum	0.156 in

General

Product Family	COMPRESSION
Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Military Specification	MS25036
Feature - Barrel Type	Standard
Feature - Barrel Style	Shrouded
Plated	Yes
Color Code	Blue
Physical Attribute - Tongue Type	Ring Terminal
Sub Brand	INSULUG
Product Type	Terminal
UPC	781810804537
Type	YAE-N
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810804537
UPC 14 Digit GTIN	00781810804537

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	99999
Carton Quantity	1000

Operational

Product Assets

Temperature Rating105° C

[Catalog \[English\]](#)



A Hubbell brand