




YAE14N78FBOX, Nylon Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAE14N78FBOX](#)



Nylon Fork Terminal For 16 - 14 AWG

Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulations
- Brazed seam provides a stronger, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance, and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability and holding power
- Smooth funnen entry for easy wire insertion

Application

Power Connector

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size Range	AN16 - AN14
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	26 mm
Dimension - Pad Width inch	0.35 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#8 - #10
Dimension - B Length fraction	4/25 in
Dimension - B Length inch	0.16 in
Dimension - Z inch	0.298 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Length Overall inch	1.01 in
Dimension - N inch	0.2 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Sub Brand	INSULUG
Color Code	Blue
Physical Attribute - Tongue Type	Fork Terminal
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Shrouded
Type	YAE-N-F
UPC 12 Digit	781810563557
UPC 14 Digit GTIN	00781810563557
Material	Copper
Plating Type	Electro Tin
UPC	781810563557

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Operational

Temperature Rating

105° C

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YAE14N78FBOX-SPEC-EN | REV 4/2026