



YAE14NBOX, Nylon Ring, 16-14 AWG, #8-10 Stud

By Burndy
Catalog # [YAE14NBOX](#)

Nylon Ring Terminal For 16 - 14 AWG, #8-10 Stud, Multi-Finger
Insulation Grip, Deep V Groove



Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

Application

For Use On: 600 Volts Maximum, 105 Deg C Maximum

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - ETL	No
Standards - Industry Standards Met	• UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Str Aircraft Size	• AN 16 • AN 14
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	16 AWG - 14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	23 mm
Dimension - Hole Size inch	0.20 in
Dimension - Strip Length inch	3/16
Dimension - Stud Size inch	• #8 • #10
Dimension - Bolt Size fraction	#8 - #10
Dimension - B Length fraction	1/4 in
Dimension - Z inch	0.28 in
Dimension - B Length inch	0.25 in
Dimension - N inch	0.16 in
Dimension - Length Overall inch	0.92 in

General

Product Family	COMPRESSION
Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Military Specification	MS25036
Feature - Barrel Style	Shrouded
Plated	Yes
Color Code	Blue
Physical Attribute - Tongue Type	Ring
Sub Brand	INSULUG
Product Type	Terminal
UPC	781810563007
Type	YAE-N
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810563007
UPC 14 Digit GTIN	00781810563007

Logistics

Pallet Quantity	99999
Carton Quantity	1200

Operational

Temperature Rating	105°C
--------------------	-------



A Hubbell brand