



YAE18N105BFBOX, Nylon Block Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAE18N105BFBOX](#)

Nylon Block Fork Terminal For 22 - 18 AWG



Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

Power Connector

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	22 - 18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.79 in

Dimension - L Length Overall mm	24 mm
Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#6 - #8
Dimension - Length Overall inch	0.95 in

General

Sub Brand	INSULUG
Insulation Type	Nylon
Color Code	Red
Physical Attribute - Tongue Type	Block Fork
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Type	Standard
Insulation Type	YAE-N
UPC 12 Digit	781810524596
UPC 14 Digit GTIN	00781810524596
Material	Copper
Plating Type	Unplated
UPC	781810524596

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	1

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)