



YAE18N1M, Nylon Ring Terminal For 22 - 18 AWG (Tape Mounted)

By Burndy
Catalog # [YAE18N1M](#)



Nylon Ring Terminal For 22 - 18 AWG (Tape Mounted)

Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	AN 16
Conductor Size	22 - 18 AWG
Conductor - Copper Str Size Range	22 AWG - 16 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Width inch	0.07 in
Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.28 in
Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	8/47
Dimension - Bolt Size fraction	#6 - #8
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	• #6 • #8
Dimension - Length Overall inch	0.92 in
Dimension - N inch	0.16 in

General

Insulation Type	Nylon
Color Code	Red
Physical Attribute - Tongue Type	Ring
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation	Y
UPC 12 Digit	781810028759
UPC 14 Digit GTIN	00781810028759
Material	Copper
Plating Type	Tin
UPC	781810028759

Logistics

Minimum Pack Quantity	2000
-----------------------	------

Product Assets

[Catalog \[English\]](#)