



YAE22G14, Nylon Ring Terminal For 26 - 20 AWG

By Burndy
Catalog # [YAE22G14](#)

Nylon Ring Terminal For 26 - 20 AWG



Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

Application

Types YAE-G and YAE-N terminals are rated 105 Deg C and meet military standard AS25036 Class 2 and SAE-AS7928 requirements

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	Military Specified (Mil-Spec)
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	20
Conductor - Copper Str Aircraft Size	• AN 26 • AN 22 • AN 20
Conductor Size	26 - 20 AWG
Conductor - Copper Str Size Range	26 AWG - 20 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type	Ring Terminal
----------------	---------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	5/32 in
Dimension - Stud Size inch	• #6 • #8
Dimension - Z inch	0.27 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Length Overall inch	0.84 in
Dimension - N inch	0.16 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Military Specification	MS25036
Sub Brand	INSULUG
Color Code	Amber
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Style	Shrouded
Type	YAE-G
UPC 12 Digit	781810804667
UPC 14 Digit GTIN	00781810804667
Material	Copper
Plating Type	Tin
UPC	781810804667

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999



A Hubbell brand