



# YAE22N66FDU4, Nylon Ring Terminal For 26 - 20 AWG

By Burndy  
Catalog # [YAE22N66FDU4](#)

Nylon Ring Terminal For 26 - 20 AWG

## Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

## Specifications

|                               |    |
|-------------------------------|----|
| Certification - cULus         | No |
| Certification - UL Recognized | No |
| Certification - ETL           | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - CSA Approved  | No |
| UL Listed                     | No |

## Conductor

|                                      |                                                                                         |
|--------------------------------------|-----------------------------------------------------------------------------------------|
| Conductor - Copper Str Aircraft Size | <ul style="list-style-type: none"><li>• AN 26</li><li>• AN 22</li><li>• AN 20</li></ul> |
| Conductor Size                       | 26 - 20 AWG                                                                             |
| Conductor Type                       | CU C Str-Size                                                                           |

## Configuration

|                |               |
|----------------|---------------|
| Connector Type | Fork Terminal |
|----------------|---------------|

## Dimensions



|                                |                                                                                |
|--------------------------------|--------------------------------------------------------------------------------|
| Dimension - B Length fraction  | 10/91 in                                                                       |
| Dimension - B Length inch      | 0.11 in                                                                        |
| Dimension - Z inch             | 0.27 in                                                                        |
| Dimension - Pad Width inch     | 0.28 in                                                                        |
| Dimension - Hole Size fraction | 3/20                                                                           |
| Dimension - Bolt Size fraction | #4 - #6                                                                        |
| Dimension - Hole Size inch     | 0.15 in                                                                        |
| Dimension - Stud Size inch     | <ul style="list-style-type: none"><li>• #4</li><li>• #5</li><li>• #6</li></ul> |
| Dimension - N inch             | 0.12 in                                                                        |

## General

|                                  |                |
|----------------------------------|----------------|
| Insulation Type                  | Nylon          |
| Physical Attribute - Tongue Type | Fork           |
| Trade Name                       | INSULUG™       |
| Plated                           | Y              |
| Feature - Barrel Style           | Shrouded       |
| Insulation                       | Y              |
| UPC 12 Digit                     | 781810082263   |
| UPC 14 Digit GTIN                | 00781810082263 |
| Material                         | Copper         |
| Plating Type                     | Gold           |
| UPC                              | 781810082263   |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 1000  |
| Carton Quantity       | 1000  |
| Pallet Quantity       | 99999 |

## Product Assets

[Catalog \[English\]](#)