



## Cu T-Type Battery Post Connector Terminal, 1/0 AWG, Negative

By Burndy

Catalog # [YAEBAF25NTN](#)

1/0 AWG NEGATIVE T-STYLE BATTERY POST TERMINAL



Features

- Barrel is color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Supplied standard with stainless steel hardware installed
- Clamp color coded by polarity - Red is Postive, Black is Negative
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Battery Post Terminal

Specifications

|                                    |     |
|------------------------------------|-----|
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Standards - RoHS Compliant         | Yes |
| Standards - RoHS Compliance Status | CM  |
| Certification - cULus              | No  |
| UL Listed                          | No  |
| Certification - CSA Approved       | No  |

Conductor

|                                     |           |
|-------------------------------------|-----------|
| Conductor - Copper Flex G Size      | 1/0 AWG   |
| Conductor - Copper Str Compact Size | 1/0 AWG   |
| Conductor - Copper DLO Size         | 1/0 AWG   |
| Conductor Size                      | 1/0 AWG   |
| Conductor - Copper Flex H Size      | 1/0 AWG   |
| Conductor - Material                | COPPER    |
| Wire Size                           | 1/0 AWG   |
| Conductor - Copper Flex K Size      | 1/0 AWG   |
| Conductor - Copper Flex M Size      | 1/0 AWG   |
| Conductor Type                      | CODE/FLEX |
| Conductor - Copper Str Size Range   | 1/0 AWG   |
| Conductor - Copper Str Size         | 1/0 AWG   |
| Conductor - Copper Flex I Size      | 1/0 AWG   |

Configuration

|                |                |
|----------------|----------------|
| Connector Type | BATTERY T-POST |
|----------------|----------------|

Current



A Hubbell brand

|                   |       |
|-------------------|-------|
| Voltage Rating    | 35 kV |
| Voltage - Maximum | 35000 |

Dimensions

|                                   |           |
|-----------------------------------|-----------|
| Package Height                    | 0.000 in  |
| Physical Attribute - Tongue Angle | Straight  |
| Package Weight                    | 0.000 lb. |
| Package Length                    | 0.000 in  |
| Package Width                     | 0.000 in  |
| Dimension - L Length Overall      | 60 mm     |
| Dimension - Diameter Min Size     | 0.46 in   |
| Dimension - Length Overall        | 2.36 in   |
| Dimension - Strip Length inch     | 1-9/32    |

Force Related

|                     |           |
|---------------------|-----------|
| Installation Torque | 72 LBS/in |
| Recommended in-lb   |           |

General

|                   |                |
|-------------------|----------------|
| Plated            | Y              |
| Color Code        | Pink           |
| Trade Name        | HYLUG™         |
| Die Index         | 12             |
| UPC               | 781810562437   |
| Type              | OEM Terminals  |
| Material          | Copper         |
| Plating Type      | Tin Plated     |
| Finish Type       | Tin-Plated     |
| UPC 12 Digit      | 781810562437   |
| UPC 14 Digit GTIN | 00781810562437 |

Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 10  |
| Pallet Quantity       | 1   |
| Carton Quantity       | 100 |

Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|

Product Assets

[Catalog \[English\]](#)