



Cu T-Type Battery Post Connector Terminal, 2/0 AWG, Positive

By Burndy

Catalog # [YAEBAF26PTN](#)

2/0 AWG POSITIVE T-STYLE BATTERY POST TERMINAL



Features

- Barrel is color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Supplied standard with stainless steel hardware installed
- Clamp color coded by polarity - Red is Postive, Black is Negative
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Battery Post Terminal

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliant	Yes
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No


Conductor

Conductor - Copper Flex G Size	2/0 AWG
Conductor - Copper Str Compact Size	2/0 AWG
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	2/0 AWG
Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Conductor - Copper Flex M Size	2/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Flex I Size	2/0 AWG

Configuration

Connector Type	BATTERY T-POST
----------------	----------------

Current



Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	1.100 in
Physical Attribute - Tongue Angle	Straight
Package Weight	2.500 lb.
Package Length	9.300 in
Package Width	4.600 in
Dimension - L Length Overall	60 mm
Dimension - Diameter Min Size	0.50 in
Dimension - Length Overall	2.36 in
Dimension - Strip Length inch	1-9/32

Force Related

Installation Torque	72 LBS/in
Recommended in-lb	

General

Plated	Y
Color Code	Black
Trade Name	HYLUG™
Die Index	13
UPC	781810562468
Type	OEM Terminals
Material	Copper
Plating Type	Tin Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810562468
UPC 14 Digit GTIN	00781810562468

Logistics

Minimum Pack Quantity	10
Pallet Quantity	6200
Carton Quantity	100

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)