



Straight Style Battery Post Terminal, 4 AWG, Positive

By Burndy
Catalog # [YAEBAS4CPTN](#)

4 AWG POSITIVE STRAIGHT STYLE BATTERY POST TERMINAL

Features

- Barrel is color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Supplied standard with stainless steel hardware installed
- Clamp color coded by polarity - Red is Postive, Black is Negative
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Battery Post Terminal

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Str	4 AWG
Compact Size	
Conductor - Copper DLO Size	4 AWG
Conductor Size	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Material	COPPER
Wire Size	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	4 AWG
Range	
Conductor - Copper Str Size	4 AWG
Conductor - Copper Flex I Size	4 AWG

Configuration

Connector Type	BATTERY STRAIGHT POST
----------------	-----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	1.000 in
Physical Attribute - Tongue Angle	Straight
Package Weight	1.400 lb.
Package Length	8.000 in
Package Width	3.400 in
Dimension - L Length Overall	59 mm
Dimension - Length Overall	2.30 in
inch	
Dimension - Strip Length inch	1-3/32 in

Force Related

Installation Torque	72 LBS/in
Recommended in-lb	

General

Color Code	Gray
Trade Name	HYDENT™
Die Index	6
UPC	781810562543
Type	OEM Terminals
Material	COPPER
Plating Type	Tin Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810562543
UPC 14 Digit GTIN	00781810562543

Logistics

Pallet Quantity	12000
Carton Quantity	100

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand