



YAES10N14, Nylon Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAES10N14](#)

Nylon Ring Terminal For 16 - 14 AWG



Features

- Integral one-piece copper barrel / insulation grip and wire strain relief design for improved physical strength characteristics over a multi-piece design
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Brazed seam provides a stronger barrel design, minimizes any possible splitting and eliminates folding
- Deep inner barrel serrations and smooth funnel entry for excellent conductivity and pullout strength values along with easy wire insertion
- Insulation is locked in place, will not twist off, maintaining proper dielectric values
- Electro-tin plated for durable, long lasting resistance to corrosion
- Color-coded and clearly marked for quick, easy wire size identification
- Ring tongue provides a secure termination under the screw head that cannot be removed without complete removal of the screw, allowing two or more terminals to be stacked on a common stud

Application

For use on copper compression connections

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	• 12 AWG • 10 AWG
-----------------------------	---

Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.58 in
Dimension - G inch	0.4 in
Package Height	0.000 in
Dimension - Hole Size inch	0.4 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	3/8
Dimension - Bolt Size fraction	3/8
Dimension - Length Overall inch	1.33 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Military Specification	MS25036
Sub Brand	INSULUG
Color Code	Yellow
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Style	Skived
Type	YAES
UPC 12 Digit	781810805077
UPC 14 Digit GTIN	00781810805077
Material	Copper
Plating Type	Tin
UPC	781810805077

Logistics

Minimum Pack Quantity	500
Carton Quantity	500

Pallet Quantity 99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand