



# YAES14N54F, Nylon Fork Terminal For 16 - 14 AWG

By Burndy  
Catalog # [YAES14N54F](#)



Nylon Fork Terminal For 16 - 14 AWG

### Features

- Fork tongue design for faster installation
- Screw needs only to be loosened (not completely removed) for termination

### Application

Power Connector

### Specifications

|                                    |                                                                                             |
|------------------------------------|---------------------------------------------------------------------------------------------|
| Buy American Compliant             | Contact Manufacturer                                                                        |
| Certification - cULus              | No                                                                                          |
| EU RoHS Indicator                  | Yes                                                                                         |
| Certification - UL Recognized      | No                                                                                          |
| Industry Standard(s)               | <ul style="list-style-type: none"><li>UL486</li><li>Military Specified (Mil-Spec)</li></ul> |
| Buy America(n) Qualified           | Contact Manufacturer                                                                        |
| Certification - ETL                | No                                                                                          |
| Standards - Industry Standards Met | UL486                                                                                       |
| Standards - RoHS Compliance Status | CM                                                                                          |
| Certification - CSA Approved       | Yes                                                                                         |
| UL Listed                          | Yes                                                                                         |

### Conductor

|                                     |                                                                                      |
|-------------------------------------|--------------------------------------------------------------------------------------|
| Conductor - Copper Str Size         | <ul style="list-style-type: none"><li>16 AWG</li><li>14 AWG</li></ul>                |
| Conductor - Copper Solid Size       | <ul style="list-style-type: none"><li>16 AWG</li><li>15 AWG</li><li>14 AWG</li></ul> |
| Conductor - Copper Solid Size Range | 16 AWG-14 AWG                                                                        |
| Conductor Size                      | 16 - 14 AWG                                                                          |
| Conductor - Copper Str Size Range   | 16 AWG - 14 AWG                                                                      |
| Conductor Type                      | CU C Str-Size                                                                        |

### Configuration

|                                      |               |
|--------------------------------------|---------------|
| Physical Attribute - Number of Holes | 1             |
| Connector Type                       | Fork Terminal |

### Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

### Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Package Weight                  | 0.000 lb. |
| Dimension - Pad Width inch      | 0.47 in   |
| Package Height                  | 0.000 in  |
| Dimension - Hole Size fraction  | 10/37     |
| Dimension - Hole Size inch      | 0.27 in   |
| Dimension - Strip Length inch   | 7/32 in   |
| Dimension - Stud Size inch      | 1/4       |
| Dimension - Z inch              | 0.38 in   |
| Dimension - Bolt Size fraction  | 1/4       |
| Dimension - Length Overall inch | 1.03 in   |
| Dimension - N inch              | 0.24 in   |

### General

|                                  |                      |
|----------------------------------|----------------------|
| Insulation Type                  | Nylon                |
| Trade Name                       | INSULUG™             |
| Insulation                       | Y                    |
| Sub Brand                        | INSULUG              |
| Color Code                       | Blue                 |
| Physical Attribute - Tongue Type | Fork                 |
| Plated                           | Y                    |
| Feature - Barrel Type            | Standard             |
| Type                             | YAES-F               |
| UPC 12 Digit                     | 781810804841         |
| UPC 14 Digit GTIN                | 00781810804841       |
| Material                         | Copper               |
| Plating Type                     | Tin - Electro Plated |
| UPC                              | 781810804841         |

### Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 1000  |
| Carton Quantity       | 1000  |
| Pallet Quantity       | 99999 |

### Product Assets

[Catalog \[English\]](#)



A Hubbell brand