



YAEV14BOX, Nylon Ring, 16-14 AWG, #8-10 Stud

By Burndy
Catalog # [YAEV14BOX](#)

Nylon Ring Terminal For 16 - 14 AWG, #8-10 Stud, Double thick tongue for maximum reliability and electrical capacity



Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

Application

For High Vibration Applications Encountered In Aircraft And Aboard Ships
As Well As Motor Lead Applications In Hospitals, Industrials And
Generating Plants

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 18 AWG • 16 AWG • 14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Aircraft Size Range	AN 18-AN 14
Conductor - Copper Str Aircraft Size	• AN 18 • AN 16 • AN 14
Conductor Type	• CU C Str Aircraft-Size • CU C Str-Size
Conductor - Copper Str Size Range	18 AWG - 14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	24 mm
Dimension - Hole Size inch	0.20 in
Dimension - Strip Length inch	1/4
Dimension - Stud Size inch	• #8 • #10
Dimension - Bolt Size fraction	#8 - #10
Dimension - Z inch	0.24 in
Dimension - N inch	0.16 in
Dimension - Length Overall inch	0.94 in

General

Product Family	COMPRESSION
Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Plated	Yes
Color Code	Blue
Physical Attribute - Tongue Type	Ring
Sub Brand	INSULUG
Product Type	Terminal
UPC	781810023327
Type	YAEV, Heavy Duty
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810023327
UPC 14 Digit GTIN	00781810023327

Logistics

Minimum Pack Quantity	100
Carton Quantity	100

Operational

Product Assets

Temperature Rating105°C

[Catalog \[English\]](#)



A Hubbell brand