



YAEV14L33, Seamless Barrel Nylon  
Insulated #14 - #16 AWG Ring Terminal with  
#6 Stud

By Burndy  
Catalog # [YAEV14L33](#)

18-14 NYL HDTY RING

Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

Specifications

|                          |                      |
|--------------------------|----------------------|
| Buy American Compliant   | Contact Manufacturer |
| EU RoHS Indicator        | Contact Manufacturer |
| Certification - ETL      | No                   |
| Buy America(n) Qualified | Contact Manufacturer |



Configuration

|                 |   |
|-----------------|---|
| Number of Holes | 1 |
|-----------------|---|

General

|                              |              |
|------------------------------|--------------|
| Sub Brand                    | HYLUG        |
| Color                        | Blue         |
| Construction Material - Main | Copper       |
| Finish Type                  | Tin-Plated   |
| UPC                          | 621945486843 |

Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 10000 |
| Carton Quantity       | 1000  |
| Pallet Quantity       | 99999 |

Product Assets

[Catalog \[English\]](#)