



YAEV14R1, Seamless Terminal Nylon Insulated #14 AWG #8 Stud 90 Degree

By Burndy
Catalog # [YAEV14R1](#)

Nylon Right Angle Ring Terminal For 16 - 14 AWG



Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

Specifications

Certification - cULus	N
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	N
Certification - ETL	No
Standards - Industry Standards Met	• UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Solid Size	• 18 AWG • 17 AWG • 16 AWG • 15 AWG • 14 AWG
Conductor - Copper Solid Size Range	18 AWG-14 AWG
Conductor - Copper Str Aircraft Size Range	N/A
Conductor - Copper Str Navy Size Range	N/A
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 18 AWG • 16 AWG • 14 AWG

Conductor - Copper Str Size Range	18 AWG-14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Ring Terminal
----------------	---------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	0 mm
Dimension - Pad Width inch	0.38 in
Physical Attribute - Tongue Angle	90 Degree
Package Height	0.000 in
Length	0.52 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Hole Size inch	0.17 in
Dimension - Stud Size inch	6-8 in
Width	0.33 in
Height	0.04 in
Dimension - Thread Size	-
Dimensions	0.52 in x 0.33 in x 0.04 in

General

Insulation Type	Nylon
Color Code	Blue
Physical Attribute - Tongue Type	Ring
Trade Name	INSULUG
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Belled
Insulation	Y
UPC 12 Digit	781810459836
UPC 14 Digit GTIN	00781810459836
Material	Copper
Plating Type	Tin
Finish Type	Tin Plated Copper

UPC

781810459836

Pallet Quantity

99999

Logistics

Minimum Pack Quantity

1000

Carton Quantity

1000

Product Assets

[Catalog \[English\]](#)



A Hubbell brand