



YAG28LTC516FX, 4/0 Flex Cu, 5/16" Stud, Standard Barrel

By Burndy

Catalog # [YAG28LTC516FX](#)

4/0 Flex G,H,I,K,M,DLO, 4/0 AWG, CU, 1 Hole, 5/16 Stud, Standard Barrel



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instruction

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	4/0 AWG
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex K Size	"4/0 AWG"
Conductor - Copper Flex M Size	"4/0 AWG"
Conductor - Copper Str Size	"4/0 AWG"
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper Flex G Size	"4/0 AWG"
Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper Str Compact Size	"4/0 AWG"
Conductor - Copper DLO Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor - Copper Flex H Size	"4/0 AWG"
Conductor - Copper Flex G Size Range	4/0 AWG

Conductor - Copper Str Navy Size	200
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	"4/0 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.14 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	5/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	59 mm
Dimension - Outside Diameter inch	0.77 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.38
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size inch	5/16
Dimension - Stud Size fraction	5/16
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1 in
Dimension - Z inch	0.36 in
Dimension - B Length inch	1.03 in
Dimension - N inch	0.34 in
Dimension - Bolt Size inch	0.3125

Dimension - Length Overall inch	2.32 in	Finish Type	Tin-Plated
		UPC 12 Digit	781810090022
		UPC 14 Digit GTIN	00781810090022
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	15	Pallet Quantity	9000
Feature - Barrel Type	Standard	Carton Quantity	100
Feature - Barrel Style	Chamfered		
Plated	Y		
Color Code	Purple	Product Assets	
UPC	781810090022	Catalog [English]	
Type	Standard Barrel, Tin Plated	Installation Manual [English]	
Material	Copper	Installation Manual [English]	
Plating Type	Tin		



A Hubbell brand