



YAG28LTC516N66FXTZ, 4/0 Flex Cu, 5/16" Stud, Std, Tin-Zinc

By Burndy

Catalog # [YAG28LTC516N66FXTZ](#)

4/0 Flex G,H,I,K,M,DLO, 4/0 AWG, CU, 1 Hole, 5/16 Stud, Standard Barrel, Tin-Zinc Plated

Features

- No inspection window is ideal for more corrosive environments as the barrel transition is not open
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the wire strands during insertion
- 45° and 90° angular lugs are available
- please contact Customer Service
- Tin-Zinc plated for battery connectors or other heavy duty equipment, reduce the corrosion from lead/acid batteries
- Connectors are clearly marked with stamping and barrel color coding
- Connectors accommodate both Flex and Code Wire

Application

Wire Termination

Specifications

Buy American Compliant	No
EU RoHS Indicator	No
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Flex G Size	"4/0 AWG"
Conductor - Copper DLO Size	4/0 AWG
Range	
Conductor - Copper Str	"4/0 AWG"
Compact Size	
Conductor - Copper DLO Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor - Copper Flex H Size	"4/0 AWG"
Conductor - Copper Flex G Size	4/0 AWG
Range	
Conductor - Copper Str Navy	200 (61) Navy
Size Range	
Conductor - Copper Str Navy	200
Size	
Conductor - Material	COPPER
Wire Size	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Range	
Conductor - Copper Flex K Size	"4/0 AWG"
Conductor - Copper Flex M Size	"4/0 AWG"
Conductor Type	CODE/FLEX



Conductor - Copper Str Size	4/0 AWG
Range	
Conductor - Copper Str Size	"4/0 AWG"
Conductor - Copper Flex H Size	4/0 AWG
Range	
Conductor - Copper Flex I Size	"4/0 AWG"
Conductor - Copper Flex I Size	4/0 AWG
Range	

Configuration

Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Dimensions

Dimension - Pad Width inch	1.14 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Dimension - Bolt Size fraction	5/16
Length	2.64 in
Thickness	0.15 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.03 in
Height	0.77 in
Width	1.14 in
Dimension - Hole Size mm	10 mm
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size inch	0.38
Dimension - Strip Length inch	1-1/16 in
Dimension - Stud Size inch	5/16 in
Dimension - Stud Size fraction	5/16
Dimensions	2.64 in x 1.14 in x 0.77 in

General

Color	Purple
Color Code	Purple
Trade Name	HYLUG™
Die Index	15
UPC	621945556331
Type	Cable to Flat
Construction Material - Main	COPPER TUBING TIN - ZINC PLATED
Material	Copper
Finish Type	Tin-Zinc

Logistics

Pallet Quantity	6000
Carton Quantity	25

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)



A Hubbell brand