



YAG2CLTC14FX, 2 Flex Cu, 1/4" Stud, Standard Barrel

By Burndy

Catalog # [YAG2CLTC14FX](#)

2 Flex G,H,I,K,M,DLO, 2 AWG, CU, 1 Hole, 1/4 Stud, Standard Barrel



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instruction

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"

Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Navy Size	60
Conductor - Copper Solid Size	2 AWG
Conductor - CopperWeld Str Size	• 2 A AWG • 2 F AWG • 2 G AWG • 2 J AWG • 2 K AWG • 2 N AWG • 2 P AWG

Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	"2 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.68 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	42 mm
Dimension - Outside Diameter inch	0.46 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	11/16 in

Dimension - Stud Size inch	1/4 in	Color Code	Brown
Dimension - Stud Size fraction	1/4	Physical Attribute - Tongue	Straight
Dimension - Bolt Hole Size inch	0.27 in	Type	
Dimension - Bolt Size fraction	1/4	UPC	781810158586
Physical Attribute - Tongue	Straight	Type	Standard Barrel, Tin Plated
Angle		Material	Copper
Dimension - B Length fraction	5/8	Plating Type	Tin
Dimension - Z inch	0.33 in	Finish Type	Tin-Plated
Dimension - B Length inch	0.63 in	UPC 12 Digit	781810158586
Dimension - N inch	0.31 in	UPC 14 Digit GTIN	00781810158586
Dimension - Bolt Size inch	0.25		
Dimension - Length Overall	1.64 in		
inch			
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	10	Carton Quantity	50
Feature - Barrel Type	Standard		
Feature - Barrel Style	Chamfered		
Plated	Y	Product Assets	
		Catalog [English]	
		Installation Manual [English]	
		Installation Manual [English]	

