



2 Flex G,H,I,K,M, DLO, 2 AWG, Cu, 3/8" Stud, Standard Barrel

By Burndy

Catalog # [YAG2CLTC38FX](#)

2 Flex G,H,I,K,M,DLO, 2 AWG, CU, 1 Hole, 3/8 Stud, Standard Barrel



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instruction

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"
Conductor - Copper Flex G Size Range	2 AWG

Conductor - Copper Str Navy Size Range 60 (37) Navy

Conductor - Copper Str Navy Size 60

Conductor - Copper Solid Size 4 AWG

Conductor - CopperWeld Str Size

- 2 A AWG
- 2 F AWG
- 2 G AWG
- 2 J AWG
- 2 K AWG
- 2 N AWG
- 2 P AWG

Conductor Type CODE/FLEX

Conductor - Copper Str Size Range 2 AWG

Conductor - Copper Flex H Size Range 2 AWG

Conductor - Copper Flex I Size "2 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.58 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	42 mm
Dimension - Outside Diameter inch	0.41 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1/2 in
Dimension - Stud Size inch	3/8 in
Dimension - Stud Size fraction	3/8

Dimension - Bolt Hole Size inch	0.40 in	Physical Attribute - Tongue	Straight
Dimension - Bolt Size fraction	3/8	Type	
Physical Attribute - Tongue	Straight	UPC	781810194379
Angle		Type	Standard Barrel, Tin Plated
Dimension - B Length fraction	1/2	Material	Copper
Dimension - Z inch	0.42 in	Plating Type	Tin
Dimension - B Length inch	0.50 in	Finish Type	Tin-Plated
Dimension - N inch	0.41 in	UPC 12 Digit	781810194379
Dimension - Bolt Size inch	0.38	UPC 14 Digit GTIN	00781810194379
Dimension - Length Overall	1.67 in		
inch			
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	5
Die Index	10	Pallet Quantity	48000
Feature - Barrel Type	Standard	Carton Quantity	50
Feature - Barrel Style	Chamfered		
Plated	Y	Product Assets	
Color Code	Brown	Catalog [English]	
		Installation Manual [English]	
		Installation Manual [English]	

