



YAG34LTC516N66FXTZ, Cu Compression, 1-Hole, 5/16" Stud, Standard Barrel, Tin-Zinc Plated, 350 kcmil

By Burndy

Catalog # [YAG34LTC516N66FXTZ](#)

350 kcmil G,H,I,K,M,373 DLO, CU, 1 Hole, 5/16 Stud, Standard Barrel, Tin-Zinc Plated

Features

- No inspection window is ideal for more corrosive environments as the barrel transition is not open
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the wire strands during insertion
- 45° and 90° angular lugs are available
- please contact Customer Service
- Tin-Zinc plated for battery connectors or other heavy duty equipment, reduce the corrosion from lead/acid batteries
- Connectors are clearly marked with stamping and barrel color coding
- Connectors accommodate both Flex and Code Wire

Application

Wire Termination

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Flex G Size	350 KCMIL
Conductor - Copper DLO Size	373 kcmil
Range	
Conductor - Copper DLO Size	373 KCMIL
Conductor Size	350 KCMIL
Conductor - Copper Flex H Size	350 KCMIL
Conductor - Copper Flex G Size	350 kcmil
Range	
Conductor - Material	COPPER
Wire Size	350 KCMIL
Conductor - Copper Flex K Size	350 kcmil
Range	
Conductor - Copper Flex K Size	350 KCMIL
Conductor - Copper Flex M Size	350 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	350 kcmil
Range	
Conductor - Copper Str Size	350 KCMIL



Conductor - Copper Flex H Size 350 kcmil
Range

Conductor - Copper Flex I Size 350 KCMIL

Conductor - Copper Flex I Size 350 kcmil
Range

Configuration

Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Dimensions

Dimension - Pad Width inch	1.54 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Dimension - Bolt Size fraction	5/16
Length	3.09 in
Thickness	0.23 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.27 in
Height	1.06 in
Width	1.55 in
Dimension - Hole Size mm	10 mm
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size inch	0.38
Dimension - Strip Length inch	1-5/16 in
Dimension - Stud Size inch	5/16 in
Dimension - Stud Size fraction	5/16
Dimensions	3.09 in x 1.55 in x 1.06 in

General

Color	Blue
Color Code	Blue
Trade Name	HYLUG™
Die Index	19
UPC	621945556324
Type	Cable to Flat
Construction Material - Main	COPPER TUBING TIN - ZINC PLATED
Material	Copper
Finish Type	Tin-Zinc

Logistics

Pallet Quantity 5800
Carton Quantity 25

Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [English]



A Hubbell brand