



YAG36LTC38FX, Compression Terminal, 500 kcmil G,H, 444 DLO, Cu, 1-Hole, 3/8" Stud, Standard Barrel

By Burndy

Catalog # [YAG36LTC38FX](#)

500 kcmil G, H, 444 DLO, CU, 1 Hole, 3/8 Stud, Standard Barrel

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instruction

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	500 KCMIL
Conductor - Copper Flex K Size	450 kcmil
Conductor - Copper Flex M Size	450 kcmil
Conductor - Copper Str Size	500 KCMIL
Conductor - Copper Flex G Size	500 KCMIL
Conductor - Copper DLO Size	444 kcmil
Range	
Conductor - Copper DLO Size	444 KCMIL
Conductor Size	500 KCMIL
Conductor - Copper Flex H Size	500 KCMIL
Conductor - Copper Flex G Size	500 kcmil
Range	
Conductor Type	FLEX
Conductor - Copper Str Size	500 kcmil
Range	
Conductor - Copper Flex H Size	500 kcmil
Range	
Conductor - Copper Flex I Size	450 kcmil



Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.73 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	83 mm
Dimension - Outside Diameter inch	1.19 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1/2 in
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-3/8 in
Dimension - Z inch	0.42 in
Dimension - B Length inch	1.38 in
Dimension - N inch	0.50 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	3.27 in

General

Trade Name	HYLUG™
Die Index	20
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y

Color Code	Brown
UPC	781810259108
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810259108
UPC 14 Digit GTIN	00781810259108

Logistics

Minimum Pack Quantity	20
Pallet Quantity	2960
Carton Quantity	10

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)



A Hubbell brand