



YAG6CL2TC14FXTZ, Compression Terminal, 6 Flex G,H,I,K,M, DLO, 6 AWG, Cu, 2-Hole, 1/4" Stud, 5/8" Spacing, Standard Barrel

By Burndy
Catalog # [YAG6CL2TC14FXTZ](#)



6 Flex G,H,I,K,M,DLO, 6 AWG CU, Two Hole, 1/4 Stud Size, 5/8 Standard Barrel, Internal Chamfer, Tin-Zinc Plated, UL/CSA, 90°C, Up to 35kV, Blue Color Code, 7 or 374 Die Index.

Features

- No inspection window is ideal for more corrosive environments as the barrel transition is not open
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the wire strands during insertion
- 45° and 90° angular lugs are available
- please contact Customer Service
- Tin-Zinc plated for battery connectors or other heavy duty equipment, reduce the corrosion from lead/acid batteries
- Connectors are clearly marked with stamping and barrel color coding
- Connectors accommodate both Flex and Code Wire

Application

Wire Termination

General

Catalog Number	YAG6CL2TC14FXTZ
Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	7
Finish Type	Tin-Zinc
Material	COPPER
Trade Name	HYLUG™
Type	Cable to Flat
UPC	621945555792

Dimensions

Dimension - B Length inch	0.50 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	1/2 in
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4 in

Length	2.06 in
Thickness	0.08 in

Conductor Related

Conductor - Copper DLO Size	6 AWG
Conductor - Copper DLO Size Range	6 AWG
Conductor - Copper Flex G Size	"6 AWG"
Conductor - Copper Flex G Size Range	6 AWG
Conductor - Copper Flex H Size	"6 AWG"
Conductor - Copper Flex H Size Range	6 AWG
Conductor - Copper Flex I Size	"6 AWG"
Conductor - Copper Flex I Size Range	6 AWG
Conductor - Copper Flex K Size	"6 AWG"
Conductor - Copper Flex K Size Range	6 AWG
Conductor - Copper Flex M Size	"6 AWG"
Conductor - Copper Str Compact Size	"6 AWG"
Conductor - Copper Str Navy Size	40
Conductor - Copper Str Size	"6 AWG"
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE/FLEX
Wire Size	6 AWG

Certifications And Compliance

Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024)
Certification - CSA Approved Industry Standard(s)	Yes UL 486A-486B

Logistics

Carton Quantity	100
Pallet Quantity	24000

Product Assets

- Catalogs - BURNDY Master Catalog - Section C - Compression Connections
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

- Installation Manuals - Medium & Large HYDENT Copper & Aluminum Terminal Crimp Instructions with 750 Series 12-Ton Tool
- Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Sales Drawings - 50106783
- Specifications - YAG6CL2TC14FXTZ
- Video - HYDENT Compression Terminal Overview Video



A Hubbell brand