



YAGB27LTC38FX, Battery Terminal, 3/0 AWG, 1-Hole, 3/8" Stud

By Burndy

Catalog # [YAGB27LTC38FX](#)

3/0 AWG, 3/8 Stud Size, One Hole Cu Battery Terminal



Features

- Color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper DLO Size	3/0 AWG
Range	
Conductor - Copper DLO Size	3/0 AWG
Conductor Size	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG
Conductor - Copper Flex G Size	3/0 AWG
Range	
Conductor - Material	COPPER
Wire Size	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Range	
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	3/0 AWG
Range	
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG
Range	
Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG
Range	

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	GROUNDING/STARTER LUGS

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Hole Size mm	10.4 mm
Dimension - Bolt Size inch	0.38
Dimension - Hole Size inch	0.41
Dimension - Stud Size inch	3/8 in
Dimension - Stud Size fraction	3/8

General

Color Code	Orange
Trade Name	HYLUG™
Die Index	14
UPC	781810565803
Type	OEM Terminals
Material	Copper
Finish Type	Tin-Plated
UPC 12 Digit	781810565803
UPC 14 Digit GTIN	00781810565803

Logistics

Minimum Pack Quantity	20
Pallet Quantity	1
Carton Quantity	200

Product Assets

[Catalog \[English\]](#)