



YAGB28LTC12FX90RT, Battery Terminal, 4/0 AWG, 1-Hole, 1/2" Stud

By Burndy

Catalog # [YAGB28LTC12FX90RT](#)

4/0 AWG, 1/2 Stud Size, One Hole Cu Battery Terminal



Features

- Color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper DLO Size	4/0 AWG
Range	
Conductor - Copper DLO Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex G Size	4/0 AWG
Range	
Conductor - Material	COPPER
Wire Size	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Range	
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	4/0 AWG
Range	
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Range	
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Range	

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	GROUNDING/STARTER LUGS

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	90 Degree
Dimension - L Length Overall	65 mm
mm	
Dimension - Hole Size mm	13.5 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.53
Dimension - Length Overall	2.56 in
inch	
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size fraction	1/2

General

Color Code	Purple
Trade Name	HYLUG™
Die Index	15
UPC	781810563144
Type	OEM Terminals
Material	Copper
Finish Type	Tin-Plated
UPC 12 Digit	781810563144
UPC 14 Digit GTIN	00781810563144

Logistics

Minimum Pack Quantity	20
-----------------------	----

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand