



YAK25A2G2, Aluminum Stacking Terminal

By Burndy
Catalog # [YAK25A2G2](#)



Aluminum Stacking compression terminal, 1/0 Str., 5.62 IN L, Up to eight conductors can be stacked on one 4 hole pad

Features

- Aluminum Stacking Compression Terminal
- 2-NEMA Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Copper Str Size	1/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.91 in
Dimension - Bolt Hole Size inch	0.50 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	159 mm
Dimension - B Length inch	1.1 in
Dimension - Outside Diameter inch	0.65 in
Dimension - D inch	3.06 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.62 in
Dimension - Strip Length inch	1-3/16 in

General

Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard
Die Index	- K-5/8 - BG 243
UPC	781810081693
Material	Aluminum Alloy
UPC 12 Digit	781810081693
UPC 14 Digit GTIN	00781810081693

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)