

YAK28A2G2, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAK28A2G2](#)



Cast Al Straight Stacking Lug, 2-NEMA Holes, 4/0 Str Al/Cu,
0.56" Hole Dia

Features

- Cast Aluminum Straight Stacking Lug
- 2-NEMA Holes
- 4/0 Str Al/Cu

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.17 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm	157 mm
Dimension - Outside Diameter inch	0.91 in
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	1-3/4 in
Dimension - Bolt Hole Size inch	0.50 in
Physical Attribute - Tongue Angle	Offset
Dimension - B Length inch	1.52 in
Dimension - D inch	3.06 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	6.20 in

General

Trade Name	HYLUG™
Die Index	• 249 • K-840
Feature - Barrel Style	Chamfered
Plated	N
Physical Attribute - Tongue Type	Standard
UPC	781810186855
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810186855
UPC 14 Digit GTIN	00781810186855

Logistics

Minimum Pack Quantity	4
Pallet Quantity	1
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)