



YAK29A2G2, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAK29A2G2](#)



Cast Al Straight Stacking Lug, 2-NEMA Holes, 250 kcmil, 0.56" Hole Dia

Features

- Cast Al Straight Stacking Lug
- 2-NEMA Holes
- 250 kcmil

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	250 kcmil
Conductor - AL Str Size Range	250 kcmil
Conductor - Copper Str Size Range	250 kcmil
Conductor - Copper Str Size	250 kcmil

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.62 in
Dimension - Bolt Hole Size inch	0.50 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	174 mm
Dimension - B Length inch	1.91 in
Dimension - Outside Diameter inch	1.11 in
Dimension - D inch	3.06 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	6.84 in
Dimension - Strip Length inch	2 in

General

Feature - Barrel Style	Chamfered
Plated	N
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard
Die Index	• 299 • 705
UPC	781810186954
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810186954
UPC 14 Digit GTIN	00781810186954

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)