

YAK2CA2G2, Aluminum Stacking Terminal

By Burndy
Catalog # [YAK2CA2G2](#)



Aluminum Stacking compression terminal, 2 Str., 5.62 IN L, Up to eight conductors can be stacked on one 4 hole pad

Features

- Aluminum Stacking compression terminal
- 2 Str
- Up to eight conductors can be stacked on one 4 hole pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor - Copper Str Size	2 AWG
Range	
Conductor - Copper Str Size	2 AWG

Configuration

Physical Attribute - Number of	1
Crimps Required	

Dimensions

Dimension - Pad Width inch	0.91 in
Dimension - Bolt Hole Size inch	0.50 in
Package Height	0.000 in
Physical Attribute - Tongue	Straight
Angle	
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall	143 mm
mm	
Dimension - B Length inch	1.1 in
Dimension - Outside Diameter	0.65 in
inch	
Dimension - D inch	3.06 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall	5.62 in
inch	
Dimension - Strip Length inch	1-3/16 in

General

Plated	N
Trade Name	HYLUG™
Physical Attribute - Tongue	Standard
Type	
Die Index	• K-5/8 • BG • 243
UPC	781810081716
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810081716
UPC 14 Digit GTIN	00781810081716

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1
Carton Quantity	26

Product Assets

[Catalog \[English\]](#)