



YAK34A2G2, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAK34A2G2](#)



Cast Al Straight Stacking Lug, 2-NEMA Holes, 500 kcmil Al, 500 kcmil Al Compressed, 0.56" Hole Dia

Features

- Aluminum Compression Stacking Terminal

Application

For Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Configuration

Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.62 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	197 mm
Dimension - Outside Diameter inch	1.25 in
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	2-1/2 in
Dimension - Bolt Hole Size inch	0.50 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length inch	2.41 in
Dimension - D inch	3.06 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	7.75 in

General

Trade Name	HYLUG™
Die Index	317 705
Feature - Barrel Style	Chamfered
Plated	N
Physical Attribute - Tongue Type	Standard
Sub Brand	TERMINALS, HYLUG
UPC	781810802281
Type	YAK-A-2G, Stacking Lug
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810802281
UPC 14 Digit GTIN	00781810802281

Logistics

Minimum Pack Quantity	3
Pallet Quantity	1
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)



A Hubbell brand