

YAK39A2G1, Aluminum - Compression  
Stacking Terminal (HYLUG Terminal)

By Burndy  
Catalog # [YAK39A2G1](#)



Cast Al Offset Stacking Lug, 2-NEMA Holes, 700 - 750 kcmil,  
0.56" Hole Dia

Features

- Cast Al Offset Stacking Lug
- 2-NEMA Holes
- 700 - 750 kcmil

Specifications

|                               |    |
|-------------------------------|----|
| Certification - UL Recognized | No |
| Certification - cULus         | No |
| Certification - ETL           | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

Conductor

|                                   |           |
|-----------------------------------|-----------|
| Conductor - AL Str Size           | 700 kcmil |
| Conductor - AL Str Size Range     | 700 kcmil |
| Conductor - Copper Str Size       | 700 kcmil |
| Conductor - Copper Str Size Range | 700 kcmil |

Configuration

|                                                |          |
|------------------------------------------------|----------|
| Physical Attribute - Number of Crimps Required | 1        |
| Physical Attribute - Number of Holes           | 2        |
| Connector Type                                 | Terminal |

Dimensions

|                                 |           |
|---------------------------------|-----------|
| Dimension - Pad Width inch      | 1.62 in   |
| Package Height                  | 0.000 in  |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 209 mm    |

|                                   |          |
|-----------------------------------|----------|
| Dimension - Outside Diameter inch | 1.5 in   |
| Dimension - Hole Size inch        | 0.56 in  |
| Dimension - Strip Length inch     | 2-3/4 in |
| Dimension - Bolt Hole Size inch   | 0.50 in  |
| Physical Attribute - Tongue Angle | Offset   |
| Dimension - B Length inch         | 2.65 in  |
| Dimension - D inch                | 3.06 in  |
| Dimension - N inch                | 0.62 in  |
| Dimension - Length Overall inch   | 8.22 in  |

General

|                                  |                                                                                   |
|----------------------------------|-----------------------------------------------------------------------------------|
| Trade Name                       | HYLUG™                                                                            |
| Die Index                        | <ul style="list-style-type: none"><li>• 608</li><li>• 722</li><li>• 786</li></ul> |
| Feature - Barrel Style           | Chamfered                                                                         |
| Plated                           | N                                                                                 |
| Physical Attribute - Tongue Type | Standard                                                                          |
| UPC                              | 781810187302                                                                      |
| Material                         | Aluminum Alloy                                                                    |
| Plating Type                     | Unplated                                                                          |
| UPC 12 Digit                     | 781810187302                                                                      |
| UPC 14 Digit GTIN                | 00781810187302                                                                    |

Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 3 |
| Pallet Quantity       | 1 |
| Carton Quantity       | 1 |

Product Assets

[Catalog \[English\]](#)