

YAK39A2G2, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAK39A2G2](#)

Al Stacking Terminal Lug, 750 kcmil(Al), 1.75" Spacing



Features

- Aluminum Compression Stacking Terminal

Application

For Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	750 kcmil
Conductor - AL Str Size Range	750 kcmil
Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.62 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	209 mm
Dimension - Outside Diameter inch	1.5 in
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	2-3/4 in
Dimension - Bolt Hole Size inch	0.50 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length inch	2.65 in
Dimension - D inch	3.06 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	8.22 in

General

Trade Name	HYLUG™
Die Index	608 722 786
Feature - Barrel Style	Chamfered
Plated	No
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG, TERMINALS
Product Type	Compression
UPC	781810187357
Type	YAK-A-2G, Stacking Lug
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810187357
UPC 14 Digit GTIN	00781810187357

Logistics

Minimum Pack Quantity	3
Pallet Quantity	1
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)