



YAK44A2NG8, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy
Catalog # [YAK44A2NG8](#)

Cast Al Terminal Offset Lug, Stacking Hylug, 2 Holes, 1000 kcmil, 302 Index, 0.56" Hole Dia

Features

- Cast Al Terminal Offset Stacking HYLUG
- 2 Holes
- 1000 kcmil

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1000 kcmil
Conductor - AL Str Size Range	1000 kcmil

Configuration

Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2

Dimensions

Dimension - Pad Width inch	1.62 in
Dimension - Bolt Hole Size inch	0.50 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	226 mm
Dimension - B Length inch	2.97 in
Dimension - Outside Diameter inch	1.84 in
Dimension - D inch	3.18 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	8.88 in

General

Feature - Barrel Style	Chamfered
Plated	N
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Standard
Die Index	302
UPC	781810187555
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	781810187555
UPC 14 Digit GTIN	00781810187555

Logistics

Minimum Pack Quantity	5
Pallet Quantity	216
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)